



SPECIFICATION SHEET

22-900



KUT GARD® SEAMLESS KNIT DYNEEMA® BLENDED ANTIMICROBIAL GLOVE – MEDIUM WEIGHT

- Seamless knit construction provides comfort, fit, and dexterity
- Dyneema® blend enhances the gloves performance without sacrificing flexibility or dexterity and ensures maximum protection
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- Special non-latex cuff dramatically reduces cuff blowout, even after multiple launderings in bleach
- Can be worn on its own or as a glove liner
- Good gripping properties
- Shrink resistant
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199
- Antimicrobial gloves are non-toxic and non-corrosive and complies with FDA, EPA, NSF and USDA standards for food contact

APPLICATIONS

- Food service and processing
- Glass and metal handling

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using low speed. Tumble dry on low to medium heat setting. Temperature settings not to exceed 149°F (65°C). Can be dry-cleaned.

TECHNICAL DATA

MATERIAL	Dyneema® / Stainless Steel / Synthetic Fibers
CONSTRUCTION	7 gauge ambidextrous seamless knit
COLOR	■ Gray
CUFF STYLE	Knitted elasticized wrist
SIZES	XS - XL
PACKAGING	24 each per case
CASE DIMENSIONS	12.0" x 6.0" x 6.0" / 30.5cm x 15.3cm x 15.3cm
CASE WEIGHT	2.8 lbs / 1.3 kg
COO	USA

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A7 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 5

BARCODES

ITEM	EACH	DOZEN	CASE
■ 22-900/XS	---	01616314017667	02616314017667
■ 22-900/S	---	01616314017674	02616314017674
■ 22-900/M	---	01616314017681	02616314017681
■ 22-900/L	---	01616314017698	02616314017698
■ 22-900/XL	---	01616314017704	02616314017704



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	8.25 / 21.0	10.0 / 25.4	11.0 / 27.9	11.5 / 29.2	12.0 / 30.5
B	3.5 / 8.9	3.75 / 9.5	4.25 / 10.8	4.5 / 11.4	4.5 / 11
H	■ Black	■ Yellow	■ Blue	□ White	■ Green

