



# SPECIFICATION SHEET

## 263-41003

### SECURE™ 3 PASSIVE EAR MUFFS - HEADBAND

- Lightweight and durable, with soft and wide ear cushions for increased comfort and wear time
- Slim profile design increases stability and reduces risk of snagging in confined spaces
- Smooth telescopic single-point size adjustment increases comfort, stability and wear time
- Ear and headband cushions feature snap-in system for easy replacement
- Dielectric, non-conductive
- Modern, glossy finish

### APPLICATIONS

- Low frequency noise
- Airport ground crew
- Motor racing
- Drill hammering

### TECHNICAL DATA

|             |                                                                                                                                                                                                                                                         |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| MATERIAL    | Headband: POM thermoplastic<br>Ear Cups: ABS thermoplastic<br>Spacer (color ring): ABS thermoplastic<br>Ear Cushion: Polyether & PVC-foil<br>Headband cushion: Polyether & lycra<br>Foam liner (sound absorber): Polyether<br>Buckle: POM thermoplastic |
| COLOR       | Orange / Black                                                                                                                                                                                                                                          |
| ATTENUATION | NRR: 28 dB / SNR: 33 dB                                                                                                                                                                                                                                 |
| STYLE       | Headband                                                                                                                                                                                                                                                |
| SIZE        | Adjustable                                                                                                                                                                                                                                              |
| WEIGHT      | 9.8 oz / 277 g                                                                                                                                                                                                                                          |
| PACKAGING   | 20 per case                                                                                                                                                                                                                                             |
| CASE        | 16" x 22" x 14" / 41cm x 56cm x 36cm                                                                                                                                                                                                                    |
| CASE WEIGHT | 18.7 lbs / 8.5 kg                                                                                                                                                                                                                                       |
| COO         | Sweden                                                                                                                                                                                                                                                  |

### BARCODES

| ITEM      | EACH          | DOZEN | CASE          |
|-----------|---------------|-------|---------------|
| 263-41003 | 7391441000302 | ---   | 7391441000302 |



### ATTENUATION DATA

| FREQUENCY HZ          | 125  | 250  | 500  | 1000 | 2000 | 3150 | 4000 | 6300 | 8000 | NRR |
|-----------------------|------|------|------|------|------|------|------|------|------|-----|
| Mean Attenuation dB   | 18.1 | 24.8 | 33.5 | 42.8 | 37.3 | 36.2 | 38.0 | 39.0 | 38.9 | 28  |
| Standard Deviation dB | 2.3  | 2.3  | 2.8  | 2.8  | 2.8  | 2.1  | 3.3  | 1.8  | 2.4  |     |

Tested in accordance with ANSI standard S3.19-1974

Canada Class A (L)

| FREQUENCY HZ          | 63   | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | H  | M  | L  | SNR |
|-----------------------|------|------|------|------|------|------|------|------|----|----|----|-----|
| Mean Attenuation dB   | 20,5 | 17,5 | 24,8 | 32,7 | 43,8 | 36,4 | 35,9 | 38,1 |    |    |    |     |
| Standard Deviation dB | 5,4  | 3,0  | 2,4  | 2,6  | 3,7  | 3,5  | 3,1  | 4,1  | 34 | 31 | 22 | 33  |
| APV dB                | 15,1 | 14,5 | 22,4 | 30,1 | 40,1 | 32,9 | 32,8 | 34,0 |    |    |    |     |