



SPECIFICATION SHEET

34-245



MAXIFLEX® ELITE™ ULTRA LIGHT WEIGHT SEAMLESS KNIT NYLON GLOVE WITH NITRILE COATED MICRO-FOAM GRIP

- Micro-Foam nitrile coatings are compatible with light oils and provide good grip and excellent abrasion resistance
- Raised micro dots increase durability and offer more cushioning in highly repetitive applications requiring precision handling
- 35% thinner than any other traditional foam gloves enabling it to breathe 40% more efficiently than similar gloves
- Patented micro-foam nitrile coating offers 360° breathability
- The use of an ultra light liner utilized to produce smooth and rounded fingertips, maximizing fingertip sensitivity
- Mimics the “hand at rest”, reducing hand fatigue
- The micro-cup finish allows for a controlled grip
- Consistent penetration free liner from the nitrile, leaving only the soft liner resting against the skin
- The Skin Health Alliance has awarded professional dermatological accreditation following review of the scientific dossier behind this product

APPLICATIONS

- Handling of small oily parts and components
- General assembly
- Machining
- Micro-Engineering
- Automotive components
- Logistics and warehousing

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104°F or 40°C. A mild commercial laundry detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry at temperature not exceeding 104°F (40°C).

TECHNICAL DATA

MATERIAL	Nylon liner with micro-foam nitrile coating				
COLOR	Blue				
CUFF STYLE	Continuous Knit				
SIZES	XS - XL				
PACKAGING	12 per dozen, 12 dozen per case				
CASE	22" x 14.2" x 7.9" / 56cm x 36cm x 20cm				
CASE WEIGHT	XS	S	M	L	XL
	11.9 lbs 5.4 kg	13.2 lbs 6 kg	15 lbs 6.8 kg	16.3 lbs 7.4 kg	17 lbs 7.7 kg
COO	Sri Lanka				

PERFORMANCE PROPERTIES

EN388: 4121						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5




BARCODES

ITEM	PAIR	DOZEN	CASE
34-245/XS	1616314128073	01616314128072	02616314128071
34-245/S	1616314128042	01616314128041	02616314128040
34-245/M	1616314128059	01616314128058	02616314128057
34-245/L	1616314128066	01616314128065	02616314128065
34-245/XL	1616314128090	01616314128089	02616314128088

DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	7.7 / 19.5	8.1 / 20.5	8.7 / 22	8.9 / 22.5	9.1 / 23
B	3.4 / 8.7	9.0 / 3.5	9.5 / 3.7	3.9 / 10	4.1 / 10.4
H	Blue	Red	Orange	White	Yellow



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

968 Albany Shaker Road | Latham, NY 12110 | 800-262-5755 | 518-861-0133 | Fax: 518-861-0144 | sales@pipusa.com | www.pipusa.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.