



# SPECIFICATION SHEET

## 34-800



### MAXIFOAM® PREMIUM SEAMLESS KNIT NYLON GLOVE WITH NITRILE COATED FOAM GRIP

- MaxiFoam® by ATG, premium gray foam nitrile coated palm & finger tips, white seamless knit nylon liner, 15 gauge
- Designed to channel oil away from the glove surface for excellent grip
- Ultra cool and very comfortable to wear, breathable coating
- Excellent dexterity, sensitivity, tactility, wet and dry grip
- Designed to produce minimal lint and dust;
- Minimal penetration keeps the liner soft on the inside of the glove
- Made with materials that comply with Federal regulations for food contact 21CFR, 170-199
- CFIA approved
- This style is also available tri-folded and shrink-wrapped for carefree dispensing through vending machines (34-800V)

### APPLICATIONS

- General Assembly
- Micro-engineering
- Automotive components
- Painting
- Horticulture

### CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C.

### TECHNICAL DATA

MATERIAL	Seamless nylon with nitrile coating					
COLOR	Shell: <input type="checkbox"/> White / Coating: <input checked="" type="checkbox"/> Grey					
CUFF STYLE	Continuous Knit					
SIZES	XXS - XL					
PACKAGING	12 per dozen, 12 dozen per case					
CASE	19.7" x 11.6" x 10.6" / 50cm x 29.5cm x 27cm					
CASE WEIGHT	XXS	XS	S	M	L	XL
	11.7 lbs 5.3 kg	13.0 lbs 5.9 kg	13.7 lbs 6.2 kg	15.4 lbs 7.0 kg	16.8 lbs 7.6 kg	18.1 lbs 8.2 kg
COO	Sri Lanka					

### PERFORMANCE PROPERTIES

EN388: 4131						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

### BARCODES

ITEM	BAG	DOZEN	CASE
34-800/XXS	---	01616314020377	02616314020377
34-800/XS	---	01616314017797	02616314017797
34-800/S	---	01616314017803	02616314017803
34-800/M	---	01616314017810	02616314017810
34-800/L	---	01616314017827	02616314017827
34-800/XL	---	01616314017834	02616314017834



### DIMENSIONS (in/cm)

	XXS	XS	S	M	L	XL
A	7.3 / 18.5	7.7 / 19.5	8.1 / 20.5	8.5 / 21.5	8.7 / 22.0	8.9 / 22.5
B	3.1 / 7.8	3.2 / 8.2	3.3 / 8.4	3.4 / 8.6	3.8 / 9.7	3.9 / 10.0
H	<input checked="" type="checkbox"/> Purple	<input checked="" type="checkbox"/> Blue	<input type="checkbox"/> White	<input checked="" type="checkbox"/> Green	<input checked="" type="checkbox"/> Brown	<input checked="" type="checkbox"/> Yellow

