



SPECIFICATION SHEET

40-6415



CLEANTEAM® KNIT NYLON / CARBON FIBER ELECTROSTATIC DISSIPATIVE (ESD) GLOVE WITH POLYURETHANE SMOOTH GRIP

- Electrostatic Dissipative (ESD) fiber yarns blended with low lint nylon which reduces static build-up on the glove surface for improved performance in electronics assembly
- Seamless knit gloves provide great dexterity
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- 15 gauge

APPLICATIONS

- Circuit board manufacturing
- Munitions
- Electronics assembly
- Aerospace

CARE INSTRUCTIONS

ESD Gloves can't be washed more than 2 times. Hand wash in normal temperature water (not exceeding 30° C) with a mild soap or detergent. Wash for 3-5 minutes, and rinse in cold water. Hang dry. Do not use a washing machine or tumble dry. Do not use softener or bleach.

TECHNICAL DATA

MATERIAL	Nylon / Carbon Fiber / PVC
COLOR	■ Copper / □ White
CUFF STYLE	Continuous Knit
SIZES	S & L
PACKAGING	12 pairs per dozen, 25 dozen per case
CASE SIZE	52cm x 28cm x 49cm / 20.5" x 11" x 19.3"
CASE WEIGHT	S: 23.4 lbs / 10.6 kg L: 24.5 lbs / 11.1 kg
COO	Korea

PERFORMANCE PROPERTIES

EN388: 4131						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

- Electrical Surface Resistivity (ASTM D 257:2007): Below 7.5×10^7
- Test Condition: (20+/-2)°C, (65+/-)% R.H.
- Applied Voltage: 500V, 60s

BARCODES

ITEM	BAG	DOZEN	CASE
■ 40-6415/S	---	01616314001109	02616314001109
■ 40-6415/L	---	01616314001093	02616314001093



DIMENSIONS (in/cm)

	S	L	---	---	---
A	8.7 / 22	9.7 / 24.5	---	---	---
B	3.4 / 8.5	3.7 / 9.4	---	---	---
H	■ Red	■ Blue	---	---	---

Tolerance: +/-0.5 cm

