



SPECIFICATION SHEET

40-6416



CLEANTEAM® KNIT NYLON / COPPER FIBER ELECTROSTATIC DISSIPATIVE (ESD) GLOVE WITH POLYURETHANE COATED FINGERTIPS

- Electrostatic Dissipative (ESD) fiber yarns blended with low lint nylon which reduces static build-up on the glove surface for improved performance in electronics assembly
- Seamless knit gloves provide great dexterity
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- 15 gauge

APPLICATIONS

- Circuit board manufacturing
- Munitions
- Electronics assembly
- Aerospace

CARE INSTRUCTIONS

ESD Gloves can't be washed more than 2 times. Hand wash in normal temperature water (not exceeding 30° C) with a mild soap or detergent. Wash for 3-5 minutes, and rinse in cold water. Hang dry. Do not use a washing machine or tumble dry. Do not use softener or bleach.

TECHNICAL DATA

MATERIAL	Nylon / Copper / Polyurethane
COLOR	■ Copper / □ White
CUFF STYLE	Continuous Knit
SIZES	S & L
PACKAGING	12 pairs per dozen, 25 dozen per case
CASE SIZE	52cm x 28cm x 49cm / 20.5" x 11" x 19.3"
CASE WEIGHT	S: 13.2 lbs / 6 kg L: 15.4 lbs / 7 kg
COO	Korea

PERFORMANCE PROPERTIES

- Electrical Surface Resistivity (ASTM D 257:2007): Below 7.5×10^7
- Test Condition: (20+/-)°C, (65+/-)% R.H.
- Applied Voltage: 500V, 60s

BARCODES

ITEM	BAG	DOZEN	CASE
■ 40-6416/S	---	01616314001123	02616314001123
■ 40-6416/L	---	01616314001116	02616314001116



DIMENSIONS (in/cm)

	S	L	---	---	---
A	8.3 / 21	9.7 / 23.5	---	---	---
B	3.4 / 8.5	3.7 / 9.4	---	---	---
H	■ Red	■ Blue	---	---	---
Tolerance: +/-0.5 cm					

