



40 AMP HOUR 16X14X8 SOLAR SOLUTION WITH 60 W SOLAR PANEL



The AccelTex Solutions Solar Solutions are a complete remote power solution designed for off-grid operation to power various electronics. These solar solutions are fully configured and provide multiple output power options, such as PoE and DC power.

Part Number: ATS-SOLR-40AH-60W-16148P



FEATURES

- Fully integrated unit includes charge controller, batteries, enclosure and solar panel(s)
- Multiple output power options, including PoE (802.3af & 802.3at) & 12V DC
- Multiple PoE outputs with an additional PoE Switch for powering multiple PoE devices, such as security cameras
- Batteries are continuously charged via the solar panels
- Charge controller protects against over-charging and over discharging of the batteries
- Enclosure ships with a Wall mount (Pole Mount is available as an accessory item) and Solar panel ships with a pole mount
- Outdoor-Rated



BENEFITS

- Self-Contained Unit for easy install
- Provides isolated and uninterrupted power
- Space for mounting electronics (on some models)



ADDITIONAL COMPATIBLE ACCESSORY ITEMS

- PoE Switch (ATS-POES-12VDC-56VDC)
- Enclosure Pole Mount (ATS-PMK-14)



APPLICATIONS

- Security Cameras
- Outdoor Wi-Fi
- Parking Lots and Garages
- Cellular Backhaul
- Remote Monitoring and Control
- Remote Sites
- Temporary Locations
- Disaster Relief

40 AMP HOUR 16X14X8 SOLAR SOLUTION WITH 60 W SOLAR PANEL

Part Number: ATS-SOLR-40AH-60W-16148P



MECHANICAL SPECIFICATIONS

Enclosure Weight: 44.52 lbs (20.19 kg)
Solar Panel Weight: 12.45 lbs (5.65 kg)
Total System Weight: 56.98 lbs (25.84 kg)
Enclosure Dimensions: 16" H x 14" W x 8" D (406.4 mm H x 355.6 mm W x 203.2 mm D)
Solar Panel Dimensions: 30.12" L x 25.87" H x 1.38" D (765 mm L x 657 mm H x 35 mm D)
Solar Panel Pole Mount Diameter: Up to 2" Diameter Pole (50.8 mm)
Color: Light Grey
Material: Polycarbonate
Door Type: Solid
Lock Type: Latch with Padlockable Hasp
Enclosure Installation: Mounting Feet



ELECTRICAL SPECIFICATIONS

System Output Power Options: 1 Output for 802.3af or 802.3at and 1 Output for 12V DC (Supports up to 10 Amps)
Solar Panel Input: 60W
Solar Panel Optimum Operating Current: 3.1 Amps
Charge Controller Max Input: 10 Amps



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Outdoor (NEMA 6P, 4X, 4, 3R, 122; IP68)
Operating Temperature: -4 to 122°F (-20 to 50°C)



SYSTEM COMPONENTS

- (1) 12V 40 Ah AGM Sealed Lead Acid Battery
- 16x14x8 Polycarbonate Enclosure with Solid Door, Latch Locks, Pad Lockable Hasp and Wall Mount
- Battery Tray
- 60 W Monocrystalline Solar Panel with Pole Mount
- Charge Controller (802.3af/at PoE and 12V DC, 10 Amp Output Power)
- (1) 15 cm and (1) 30 cm DIN Rail, (3) DIN Rail Mounts, (2) Universal DIN Rail Mounting Plates for equipment that is not DIN Rail Mount Ready and fasteners for equipment mounting
- (6) Battery Wiring Harnesses; (2) to controller and (4) to link batteries
- (1) PG16 and (1) PG7 Cord Grip
- (1) 85 cm Battery Safety Strap
- (1) Cable Management Supplies Kit (includes Zip Ties and Zip Tie Mounting Pads)

40 AMP HOUR 16X14X8 SOLAR SOLUTION WITH 60 W SOLAR PANEL

Part Number: ATS-SOLR-40AH-60W-16148P



RECOMMENDED SYSTTEM USAGE SCENARIOS

Watts Consumed	Total Hours of Backup**	Solar Solution Sizing*			
		12 Hour Run Time		24 Hour Run Time	
		3 Hours Peak Sunlight	6 Hours Peak Sunlight	3 Hours Peak Sunlight	6 Hours Peak Sunlight
2	120	✓	✓	✓	✓
4	60	✓	✓	✓	✓
6	40	✓	✓	✗	✓
8	30	✓	✓	✗	✓
10	24	✗	✓	✗	✗
12	20	✗	✓	✗	✗
14	17	✗	✓	✗	✗
16	15	✗	✓	✗	✗
18	13	✗	✓	✗	✗
20	12	✗	✗	✗	✗

*For all scenarios, batteries have been de-rated 50% for cold weather and recovery for non-sunny days.

**Assumptions: Batteries are fully charged and panel does not provide power (running off stored battery power only). Batteries have been derated 50% for cold weather.