



SPECIFICATION SHEET

43-850



KUT-GARD® KEVLAR® / PREOX SEAMLESS KNIT HOT MILL GLOVE WITH COTTON LINER - 32 OZ

- Seamless construction offers increased comfort and breathability
- Kevlar®/Preox blend shell provides excellent cut, abrasion and thermal protection as well as flame resistance
- 100% terry cotton lined for extra comfort
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- Open cuff allows for easy on and off
- Small size fits ladies well
- Meets OSHA CFR 1910.269 standards
- Protects against the intense heat of an electric arc complying with NFPA 70E standards

APPLICATIONS

- Hot metal handling
- Glass handling
- Foundries
- Forging operations

CARE INSTRUCTIONS

Machine wash in warm water (120°F max) with detergent rinse thoroughly, and tumble dry on low heat. Do not use fabric softeners or bleach. Can be dry cleaned for greater longevity.

TECHNICAL DATA

MATERIAL	Cotton, Preox / Kevlar®
COLOR	■ Dark Green
CUFF STYLE	Open Cuff
SIZES	One size, Large
PACKAGING	2 Dozen each per case
CASE	20" x 20" x 16" / 50.8cm x 50.8cm x 40.6cm
CASE WEIGHT	12.4 lbs / 5.6 kgs
COO	USA

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 4

BARCODES

ITEM	---	DOZEN	CASE
■ 43-850/L	---	01616314055941	02616314055940



DIMENSIONS (in/cm)

	L	---	---	---
A	11 / 27.9	---	---	---
B	5.0 / 12.7	---	---	---

