



SPECIFICATION SHEET

44-3455



4542

MAXICUT® ULTRA DT™ BY ATG®, PREMIUM BLUE ENGINEERED YARN SHELL, BLACK MICRO-FOAM 3/4 DIP NITRILE COATED W/NITRILE DOTS

- Micro-Foam nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Unique high performance yarns and fibers that offer cut protection while maintaining high levels of comfort
- Reinforcement between the thumb and forefinger
- Patented micro-foam nitrile coating offers 360° breathability making it the most breathable cut resistant glove on the market
- Optimized grip delivered through our micro-cup finish
- Minimal penetration (strike through) leaving only the soft liner resting against the skin
- The Skin Health Alliance has awarded professional dermatological accreditation following review of the scientific dossier behind this product

APPLICATIONS

- DIY
- Finishing and inspection
- Gardening
- Handling of small components
- Primary, secondary and final assembly
- Maintenance
- Logistics and warehousing
- Using tools and instruments

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Seamless knit engineered yarn, micro-foam nitrile coating					
COLOR	Blue/Black					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	12 per dozen, 6 dozen per case					
CASE	19.7" x 11.6" x 7.9" / 50cm x 29.5cm x 20cm					
CASE WEIGHT	XS 10.3 lbs 4.65 kg	S 11 lbs 5 kg	M 11.8 lbs 5.35 kg	L 12.3 lbs 5.6 kg	XL 13.2 lbs 6 kg	XXL 13.9 lbs 6.3 kg
COO	Sri Lanka					

PERFORMANCE PROPERTIES

EN388: 4542	ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16) ASTM F1790-05 ANSI Cut Level 3					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5




BARCODES

ITEM	PAIR	DOZEN	CASE
44-3455/XS	616314178467	01616314178466	02616314178465
44-3455/S	616314178375	01616314178374	02616314178373
44-3455/M	616314178368	01616314178367	02616314178366
44-3455/L	616314178351	01616314178350	02616314178359
44-3455/XL	616314178450	01616314178459	02616314178458
44-3455/XXL	616314178474	01616314178473	02616314178472

DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.3 / 21	8.7 / 22	9.1 / 23	9.3 / 23.5	9.6 / 24.5	9.8 / 25
B	3.5 / 9	3.6 / 9.2	3.9 / 9.8	4.0 / 10.2	4.2 / 10.7	4.3 / 11
H	Blue	White	Green	Brown	Yellow	Gray



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.