



# SPECIFICATION SHEET

## A10

### PACIFIC A10 USAR MEDICAL RESCUE HELMET

- Certified to EN443, NFPA 1951 - CE Paramedic Rescue/Recovery
- Compliant with ANSI Z89.1
- Lightweight Dupont™ Kevlar® composite shell weighs less than composite fiberglass and composite alternatives
- Shell is not affected by UV exposure
- Composite resins offer higher temperature resistance (up to 600°F) without distorting or melting
- High-gloss paint finish available in a variety of colors
- Ratchet headband with easy-to-adjust dial which accommodates a variety of head sizes (54-64cm)
- 3-point Nomex® chin strap c/w Pacific snapclip buckle made from fire resistance Nomex® webbing
- Internal retracting eye protection protects against hazards and blood borne pathogens
- Neck protector (optional) for ear and neck protection
- Full range of tailored Decals/Badges/Reflectorising available
- Easy on base (standard on helmet)

### APPLICATIONS

- Search and rescue
- Ambulance
- Helicopter rescue

### TECHNICAL DATA

MATERIAL	Outer Shell: Kevlar®-composite / Inner Shell: Polyurethane
SUSPENSION	Pacific Mesh liner
COLOR	<input checked="" type="checkbox"/> Blue (813-3263) <input type="checkbox"/> White (813-3263)
SIZES	OSFA, Adjustable
PACKAGING	6 per case
CASE	26.5" x 23.5" x 13" / 67.3cm x 59.7cm x 33.0cm
CASE WEIGHT	13.4 lbs / 6.08 kg
COO	New Zealand
HARM CODE	6506.10.6075

### WARRANTY

6-year limited warranty

Each helmet also carries a 2-year limited warranty on impact liners and ratchet suspensions. Internal parts including crown pads, ribbons and sweatbands are NOT covered by this warranty.

### BARCODES

ITEM	EACH	DOZEN	CASE
<input type="checkbox"/> 813-3260	616314149771		02616314149779
<input checked="" type="checkbox"/> 813-3263	616314148910		02616314148918



### DIMENSIONS (in/cm)

	OSFA				
<b>A</b>	11.2 / 28.4				
<b>B</b>	9.3 / 23.6				
<b>C</b>	7.5 / 19.1				

