

SMP3ET

Power Supply/Charger Kit

Description

Altronix SMP3ET power supply/charger converts a low voltage AC input into a 6VDC or 12VDC output. This unit has a wide range of applications for access control, security and CCTV system accessories that require additional power.



SMP3ET

Specifications

Input

Voltage 16VAC from TP1640 plug-in transformer.

Outputs

Voltage 6VDC or 12VDC selectable.
 Current 2.5A continuous max.
 Other Short circuit and thermal overload protection.
 Filtered and regulated.

Back-up Battery *(not included)*

Type Sealed lead acid or gel type.
 Failover Upon AC loss, instantaneous.

Indicators (LED)

Input Input voltage is present.
 DC Output Powered.

Physical and Environmental

Dimensions (L x W x H)
 8.5" x 7.5" x 3.5" (215.9mm x 190.5mm x 88.9mm).

Product Weight 3.3 lbs. (1.5 kg).

Shipping Weight 3.8 lbs. (1.72 kg).

Temperature

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.):

6VDC: 8 BTU/Hr.

12VDC: 15 BTU/Hr.