

SMX3000RMLV2UNC

APC Smart-UPS X 3000VA Rack/Tower LCD 100-127V with Network Card



Overview

Model Name	APC Smart-UPS X 3000VA Rack/Tower LCD 100-127V with Network Card
Includes	CD with software , Documentation CD , Installation guide , Rack Mounting brackets , Rack Mounting support rails , Rack mounting hardware , Removable support feet , Smart UPS signalling RS-232 cable , USB cable , Web/SNMP Management Card
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Canada , United States

Output

Output Power Capacity	2700 Watts / 2880 VA
Max Configurable Power (Watts)	2700 Watts / 2880 VA
Nominal Output Voltage	120V
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(1) NEMA L5-30R (Battery Backup) , (3) NEMA 5-15R (Battery Backup) , (3) NEMA 5-20R (Battery Backup)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA L5-30P
Cord Length	2.44 meters
Input voltage range for main operations	70 - 153 V
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0
Battery Slots Empty	0

Typical recharge time	3 hour(s)
Replacement Battery	APCRBC117 , CURK117-01-04
RBC Quantity	1

Communications & Management

Interface Port(s)	SmartSlot , USB
Available SmartSlot™ Interface Quantity	0
Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators , Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	540 joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
Data Line Protection	--

Physical

Maximum Height	85.0 mm
Maximum Width	432.0 mm
Maximum Depth	667.0 mm
Rack Height	2 U
Net Weight	38.46 kg
Shipping Weight	45.36 kg
Shipping Height	243.0 mm
Shipping Width	596.0 mm
Shipping Depth	869.0 mm
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	8.0
Pallet Dimensions	1000.0 mm
# of Layers per Pallet	4
# of Units per Layer per Pallet	2
Pallet Weight	388.69 kg

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	276.000 BTU/hr

Conformance

Approvals	BSMI , CSA , EN 50091-2 , EN 55022 Class A , ENERGY STAR (USA) , FCC Part 15 Class A , NOM , TUV , UL 1778 , VCCI Class A
-----------	---

Standard warranty	3 years repair or replace (excluding battery) and 2 year for battery , optional extended warranties available , optional on-site warranties available
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs