



SPECIFICATION SHEET

F6

PACIFIC F6 STRUCTURAL FIRE HELMET

- NFPA 197, AS4067
- Compliant with ANSI Z89.1
- Expected minimum service life of 15 years
- Weight is evenly distributed for balance & comfort
- Internally retracting polycarbonate One Touch™ eye guard
- Double layer flame retardant neck protector
- Full polyurethane impact liner
- Leather reinforced mesh crown provides comfort & circulation
- 20% lighter than thermo plastic helmets
- Pacific quick release buckle
- UV resistant
- Optional 4" 3mm face shield

APPLICATIONS

- Fire
- Search & Rescue
- Collapse Rescue
- Auto Extrication
- Technical Rescue

TECHNICAL DATA

MATERIAL	Outer Shell: lightweight composite
COLOR	<input type="checkbox"/> White (828-0378) <input checked="" type="checkbox"/> Red (828-0379) <input type="checkbox"/> Daisy (828-0380)
SIZES	OSFA, Adjustable
PACKAGING	7 per case
CASE	26.5" x 23.5" x 13"
CASE WEIGHT	18.48 lbs / 8.38 kg
COO	New Zealand
HARM CODE	6506.10.6075

WARRANTY

- Outer shell: 6-year limited warranty
- Neck protector: 6-month
- One Touch™ eye guard: 1-year
- Each helmet also carries a 2-year limited warranty on impact liners and ratchet suspensions. Internal parts including crown pads, ribbons and sweatbands are NOT covered by this warranty.

BARCODES

ITEM	EACH	DOZEN	CASE
<input type="checkbox"/> 828-0378	616314154461	-	02616314154469
<input checked="" type="checkbox"/> 828-0379	616314154478	-	02616314154476
<input type="checkbox"/> 828-0380	616314154485	-	02616314154483



DIMENSIONS (in/cm)

	OSFA				
A	11.4 / 29.0	-	-	-	-
B	8.3 / 22.1	-	-	-	-
C	5.9 / 15.0	-	-	-	-

