



Overview

Model Name	APC Smart-UPS RT 15kVA RM 208V
Includes	CD with software , Rack Mounting support rails , Smart UPS signalling RS-232 cable , User Manual , Web/SNMP Management Card
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Brazil , Canada , Cayman Islands , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Gambia , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	12.0 KW / 15.0 kVA
Max Configurable Power (Watts)	12.0 KW / 15.0 kVA
Nominal Output Voltage	208V
Output Voltage Note	Configurable for 208 or 240 nominal output voltage
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz user adjustable +/- 0.1
Other Output Voltages	240V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(1) Hard Wire 3-wire (2PH + G) (Battery Backup) , (2) NEMA L6-30R (Battery Backup) , (4) NEMA L6-20R (Battery Backup)
Overload Operation	60 seconds @ 125% and 30 seconds @ 150%
Bypass	Built-in Static Bypass , Internal Bypass (Automatic and Manual) , Optional External Bypass

Input

Nominal Input Voltage	208V
Input Frequency	40 - 70 Hz (auto sensing)
Input Connections	Hard Wire 3-wire (2PH + G)
Input voltage range for main operations	160 - 280 V

Other Input Voltages	240
Maximum Input Current	85 A
Input Breaker Capacity	100 A
Input Total Harmonic Distortion	Less than 5% for full load

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	4
Battery Slots Empty	0
Typical recharge time	2 hour(s)
Replacement Battery	APCRBC140
RBC Quantity	4
Nominal Battery Voltage	+/-192 V (split battery referenced to neutral)
End of Discharge Battery Voltage	+/-154 V
Efficiency in Battery Operation	93.00 %

Communications & Management

Interface Port(s)	DB-9 RS-232 , RJ-45 10/100 Base-T , Smart-Slot , SmartSlot
Available SmartSlot®; Interface Quantity	0
Pre-Installed SmartSlot®; Cards	AP9631
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms : configurable delays
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
-----------	--

Physical

Maximum Height	533.0 mm
Maximum Width	432.0 mm
Maximum Depth	773.0 mm
Rack Height	12 U
Net Weight	247.73 kg
Shipping Weight	314.09 kg
Shipping Height	990.0 mm
Shipping Width	610.0 mm
Shipping Depth	1003.0 mm
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	1.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95% non-condensing %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95% non-condensing %
Storage Elevation	0-15000 meters

Audible noise at 1 meter from surface of unit	50.000 dB
Online Thermal Dissipation	2610.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	ENERGY STAR (USA) , OSHPD , UL 1778
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Battery Notes