

Contact

Copper LAN Product Inquiry
Phone: 717-354-6200
berktek.support@nexans.com

HyperPlus 5e OSP

HyperPlus 5e OSP

Part Number: 10071496

Berk-Tek's Hyper Plus 5e OSP (Outside Plant) Standard Category 5e UTP cables are designed for outside applications, either aerial or buried in conduit or duct, where building to building interconnections must be made.

Description

Construction

24 AWG bare copper wire insulated with polyethylene. Two insulated conductors twisted together to form a pair and four such pairs cabled to form the basic unit which is injected with a water resistant flooding compound and jacketed with UV resistant polyethylene.

Standards

- North American ANSI/TIA/EIA-568-B.2 Category 5e and Category 5, ANSI/ICEA 5-56-434
- International ISO/IEC 11801 Category 5, EU Directive 2002/95/EC (RoHS)

Flame Rating: Not Flame Rated

ANSI/ICEA 5-107-704-2012, PAR 8.2.1 - Water Penetration

Applications

Berk-Tek's Hyper Plus 5e OSP UTP cable is intended for high speed data applications including:


- IEEE 802.3 1000BASE-T 1 Gb/s
- ATM 155 Mb/s 155 Mb/s
- IEEE 802.3 100BASE-TX 100 Mb/s
- CDDI 100 Mb/s
- IEEE 802.3 10BASE-T 10 Mb/s

Features

- Supports most data and voice applications
- Meets ANSI/ICEA 5-56-434 Standard for Polyolefin Insulated Communications Cables for Outdoor Use
- ETL Verified to TIA/EIA-568-B.2 Category 5e
- Fully water blocked

Benefits

- Can be used to interconnect buildings or can be run beneath a slab in duct or conduit
- Simplified structured cabling solution preserving long-term network investment
- Meets NEC requirement for cable in wet locations



Standards

National TIA/EIA-568-B.2

HyperPlus 5e OSP

HyperPlus 5e OSP

Part Number: 10071496

Characteristics

Construction characteristics	
Type of cable	UTP
Colour	Black
Dimensional characteristics	
Length per reel	1000.0 ft
Number of pairs	4
Usage characteristics	
Packaging	Reel
Field of application	Outdoor
Category	Cat. 5e
Fire safety	—

Technical Data - Physical

Technical Data - Physical			Color Code		
			Pair-1	White	Blue
Conductor	24 AWG BC		Pair-2	White	Orange
Conductor diameter—in. (mm)	0.02	(0.51)	Pair-3	White	Green
Insulated Conductor Diameter- in. (mm)	0.038	(0.96)	Pair-4	White	Brown
Cable diameter—in. (mm)	0.207	(5.3)			
Nominal cable weight—lb./kft. (kg/km)	20	(30)	Temperature Rating		
Max. installation tension—lb. (N)	25	(110)	Installation	0°C to +50°C	
Min. bend radius—in. (mm)	1	(25.4)	Operation	-20°C to +60°C	

Technical Data - Parametric Measurements

Mutual Capacitance	5.6 nF/100 m max.
DC resistance	9.38 Ohms/100 m max.
Skew	25 ns/100 m max.
Pair to ground Unbalance	330 pF/100 m max.
Velocity of Propagation	72% nom.
Input Impedance	100 ± 15% 1-100 MHz
DC Resistance Unbalance:	5% max.

Contact

Copper LAN Product Inquiry
Phone: 717-354-6200
berktek.support@nexans.com

HyperPlus 5e OSP

HyperPlus 5e OSP

Technical Data - Electrical

FREQ MHz	SRL (dB)	RL (dB)	IL (dB/100m)	PS-NEXT (dB)	NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ELFEXT (dB)	PS-ELFEXT (dB)
	min.	min.	max.	min.	min.	min.	min.	min.	min.
1	25.0	20.0	2.0	62.3	66.3	64.3	60.3	63.8	60.8
4	25.0	23.0	4.1	53.3	57.3	53.2	49.2	51.8	48.8
10	25.0	25.0	6.5	47.3	51.3	44.8	40.8	43.8	40.8
16	25.0	25.0	8.2	44.2	48.3	40.1	36	39.7	36.7
20	25.0	25.0	9.3	42.8	46.8	37.5	33.5	37.8	34.8
31.25	23.6	23.6	11.7	39.9	43.9	32.2	28.2	33.9	30.9
62.5	21.5	21.5	17.0	35.4	39.4	22.4	18.4	27.9	24.9
100	20.1	20.1	22.0	32.3	36.3	14.3	10.3	23.8	20.8

Selling information

PLEASE NOTE: In the interest of product improvement, Berk-Tek, a Nexans company may make improvements or changes in the products, the programs or services described at any time without notice. Additionally, the information contained herein may include typographical errors or technical inaccuracies. Changes will be periodically made to address any such issues.