



SPECIFICATION SHEET

94-928

PREMIUM GRADE HOT MILL GLOVE WITH THREE-LAYERS OF COTTON CANVAS AND BURLAP LINER - 28 OZ

- Three-layer cotton canvas construction offers comfort, insulation and superior heat protection
- Burlap lining for increased heat protection
- Clute cut provides a roomy fit
- Straight thumb increases comfort in closed-fisted work
- Nap-out finish for heat resistance
- Knuckle strap for extra protection
- Band Top cuff helps protect wrist area and allows for easy on and off

APPLICATIONS

- Forging
- Hot metal handling
- Castings
- Molds
- Other operations that require heat protection

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Cotton
COLOR	Natural
CUFF STYLE	Open band top
SIZES	L
PACKAGING	12 pairs per dozen, 10 dozen per case
CASE	31.5" x 11.0" x 18.5" / 80cm x 28cm x 47cm
CASE WEIGHT	46.2 lbs / 21.0 kg
COO	Pakistan

BARCODES

ITEM	BAG	DOZEN	CASE
94-928	-	01616314004162	02616314004162



DIMENSIONS (in/cm)

	L
A	10.6 / 27
B	6.1 / 15.5
C	2.4 / 6

Tolerance: 0.5cm

