



SR-20/2 SERIES SUBRACK

Fiber Equipment Rack with Power Supply

SUB RACK FRAME:

FEATURES:

- 19" EIA Sub Rack Frame
- Rear Power Bus to all plug-in cards
- Blank panels for 1, 2, and 4 slots
- 100W DC Regulated Power Supply
- 14 Card Slots Available

DIMENSIONS:

W x H x D..... 19" x 5 1/4" x 7 5/8"
Weight (with PSR-2) ... 4 1/2 lbs, 10kg

TEMPERATURE (OPERATING):

0°C to +50°C non-condensing

POWER SUPPLY:

FEATURES:

- Universal Power 100 to 240VAC
- Detachable AC line cord
- Power Switch
- Cooling Fan
- 100 Watt Switching Power Supply
- Redundant Model Available SR-20H

BLANK PANELS:

FEATURES:

Available for 1, 2 or 4 slots
Matching Black Paint
Aluminum Construction
1/4 Turn Fasteners

BPS-1 1 Slot
W x H x D..... 1" x 5" x 0.1"
Weight 1.1 oz

BPS-2 2 Slot
W x H x D..... 2" x 5" x 0.1"
Weight 2.3 oz

BPS-4 4 Slot
W x H x D..... 4" x 5" x 0.1"
Weight 4.3 oz



The American Fibertek SR-20/2 Series Fiber Equipment Sub rack is a system that can be configured with any combination of American Fibertek products including transmitters, receivers or transceivers.

The PSR-2 100 Watt power supply features a universal power input of 100 to 240 VAC with no switch selection required, high efficiency and current limiting.

All AFI part numbers beginning with the letter "R" are compatible with AFINETY. The frame, power supplies and plug in cards are all UL Listed: DRQH E194293.

Ordering Information:

SR-20/2 – SR-20 Rack Frame with PSR-2 included.

