

Zipcord Tight-Buffered Cable, Plenum

2 F, 2.0 mm diameter, 62.5 µm multimode (OM1)

CORNING

Corning zipcord cables are designed for interconnect applications. Two 900 µm buffered fibers are surrounded by aramid yarn strength members and a flame-retardant jacket. This cable design offers mechanical durability and flame resistance that meet the requirements of the National Electrical Code® (NEC®) Article 770.

This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

Meets NEC requirements

Meets burn test criteria

All-dielectric strength member

Mechanical durability


Standards

Listings


National Electrical Code®
(NEC®) OFNP, FT-6

Design and Test Criteria

NFPA 262 and CSA FT-6
(for plenum, riser and general building applications);
ICEA S-83-596



Part Number: 002K58-31130-24



Cross Section of Part Number: 002K58-31130-24

Specifications

General Specifications	
Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser, Plenum
Cable Type	Tight-Buffered
Product Type	Interconnect
Flame Rating	Plenum (OFNP)
Fiber Category	62.5 µm MM (OM1)

Zipcord Tight-Buffered Cable, Plenum

2 F, 2.0 mm diameter, 62.5 µm multimode (OM1)

CORNING

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Operation	0 °C to 70 °C (32 °F to 158 °F)

Cable Design

Fiber Count	2
Tight Buffer Color	Blue, White
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Number of Subunits	2
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Orange

Mechanical Characteristics Cable

Max. Tensile Strength, Short-Term	220 N (50 lbf)
Max. Tensile Strength, Long-Term	66 N (15 lbf)
Weight	14.6 kg/km (10 lb/1000 ft)
Nominal Outer Diameter	2.0 mm x 5.6 mm (0.11 in x 0.22 in)
Min. Bend Radius Installation	50 mm (2 in)
Min. Bend Radius Operation	14 mm (0.55 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	002K58-31130-24
Product Description	Zipcord Tight-Buffered Cable, Plenum, 2 F, 2.0 mm diameter, 62.5 µm multimode (OM1)
EAN Code	4056418186597

Zipcord Tight-Buffered Cable, Plenum

2 F, 2.0 mm diameter, 62.5 µm multimode (OM1)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Notes



**Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa**

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.
All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.