

102-66110

HellermannTyton

Article Number: 102-66110



Description: Cable Tie Strap for ATS3080, 50 lb Tensile Strength, PA66HIRHSUV, Black, 1640 ft/reel

Base Data		
	Local Order Number	ATS10266110
	Type	Strap Black ATS3080
	Color	Black (BK)
	Features and benefits	• The ATS3080 cable tie is designed for optimized material utilization by using an innovative two-piece system consisting of individual strap and closures. • Waste-free cable tie system eliminates down time due to cleaning and opening waster containers. • Bundle diameter is mechanically detected and allows a flush cut off of the strap. • Available in reels of 1,640 feet of strap and 5,000 closures.
	Quantity Per	reel
	Product Description	HellermannTyton offers the widest range of automatic cable tie tool systems which cover cable tie tensile strengths of 18, 30, and 50 pounds with bundle diameters between 1/16" to over 3". For use with HellermannTyton's Automatic Tool Systems.
	Technical Description	Cable Tie Strap for ATS3080, Black
	Short Description	Cable Tie Strap for ATS3080, 50 lb Tensile Strength, PA66HIRHSUV, Black, 1640 ft/reel
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Identification Plate Position	none
	Reel Diameter (Imperial)	15.25"
	Reel Diameter (Metric)	387mm
	Reel Length (imperial)	1640.0ft
	Reel Width (Metric)	88.9mm
	Reel Width (Imperial)	3.5"
	Releasable Closure	No
	Width W (Imperial)	0.18"
	Width W (Metric)	4.5mm
	Height H (Imperial)	0.047"

102-66110



Product Dimensions	Height H (Metric)	1.2mm
	Bundle Diameter Min. (Metric)	0.0mm
	Bundle Diameter Max. (Imperial)	3.14"
	Bundle Diameter Max. (Metric)	80.0mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +203°F (-40°C to +95°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1640
	Package Quantity (Metric)	500m
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	reel
	Reel Weight (Metric)	2.72kg
	Reel Weight (Imperial)	6lbs
	Weight (Metric)	2.7kg