

111-00829

HellermannTyton



Article Number: 111-00829

Description: Metal Content Tie, 5.9" Long, 30lb Tensile Strength, PA66MP, Blue, 100/pkg

Base Data		
	Local Order Number	111-00829
	Type	MCT30R
	Color	Blue (BU)
	Features and benefits	• Metal content dispersed throughout the head and strap ensures identification by metal detectors and X-ray machines. • Industry standard blue color assists with visual detection and reduces the risk of contamination.
	Quantity Per	bag
	Product Description	HellermannTyton's Metal Content Tie is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The tie is nylon based with metal content dispersed throughout the head and strap allowing any part of the tie to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.
	Short Description	Metal Content Tie, 5.9" Long, 30lb Tensile Strength, PA66MP, Blue, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	30.0lbs
	Minimum Tensile Strength (Metric)	135.0N
	Length L (Imperial)	5.9"
	Length L (Metric)	150.0mm
	Fixation Method	Cable Tie
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.14"
	Width W (Metric)	3.5mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm

111-00829



Product Dimensions	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	35.0mm
	Thickness T (Imperial)	0.05"
	Cable Tie Head Length (Imperial)	0.22"
	Cable Tie Head Width (Imperial)	0.24"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6, with metal particles (PA66MP)
	Material Shortcut	PA66MP
	Flammability	UL 94 HB
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	7326908595
	Content Unit (BMEcat)	pieces
	Weight (Metric)	0.7kg