

111-12215

HellermannTyton



Article Number: 111-12215

Description: Heavy-Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Red, 50/pkg

Base Data		
	Local Order Number	T120I2K2
	Type	T120I
	Color	Red (RD)
	Features and benefits	• Heavy duty design to offer higher tensile strength. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
	Quantity Per	bag
	Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Heavy-Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Red, 50/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	120.0lbs
	Minimum Tensile Strength (Metric)	535.0N
	Length L (Imperial)	11.8"
	Length L (Metric)	300.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.3"
	Width W (Metric)	7.6mm
	Cable Tie Width Max. (Imperial)	0.3"
	Cable Tie Width Max. (Metric)	7.61mm
	Bundle Diameter Min. (Imperial)	0.2"

111-12215



Product Dimensions	Bundle Diameter Min. (Metric)	5.0mm
	Bundle Diameter Max. (Imperial)	3.2"
	Bundle Diameter Max. (Metric)	80.0mm
	Cable Tie Head Length (Imperial)	0.393"
	Cable Tie Head Width (Imperial)	0.502"
	Thickness T (Metric)	1.6mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50
	Customs Number(Schedule B)	3926909987