

112-52112

# HellermannTyton



Article Number: 112-52112

Description: Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HS, Black, 100/pkg

Base Data		
	Local Order Number	CTT60R0HSC2
	Type	CTT60R
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Heat stabilized cable ties provide excellent resistance to high heat exposures.</li> <li>• Head design contains clamping rails to provide full circumferential compression around bundles.</li> <li>• Bent tail allows for quick insertion into head.</li> </ul>
	Quantity Per	bag
	Product Description	The 360 Degree compression ties were designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HS, Black, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	60.0lbs
	Minimum Tensile Strength (Metric)	265.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	205.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.19"
	Width W (Metric)	4.7mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm

112-52112

**HellermannTyton**

Product Dimensions	Bundle Diameter Max. (Imperial)	1.8"
	Bundle Diameter Max. (Metric)	45.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +257°F (-40°C to +125°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	UL   ANSI/UL 1565
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces