

157-00017

HellermannTyton

Article Number: 157-00017



Description: 1-Piece Cable Tie/Fir Tree Mount With Disc, 6.7"L, .27"-.28" Mounting Hole, PA66, Black, 100/pkg

Base Data		
	Local Order Number	157-00017
	Type	OS170
	Color	Black (BK)
	Features and benefits	• Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation. • Initial fir tree serves as a locating feature for assistance in blind assembly applications. • Disc feature provides anti-rattle protection in high vibration applications.
	Quantity Per	bag
	Product Description	Fir tree mounts, with cable ties, provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.
	Short Description	1-Piece Cable Tie/Fir Tree Mount With Disc, 6.7"L, .27"-.28" Mounting Hole, PA66, Black, 100/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	30.0lbs
	Minimum Tensile Strength (Metric)	147N
	Length L (Imperial)	6.7"
	Length L (Metric)	170.0mm
	Length L2 (Imperial)	0.6"
	Fixation Method	Fir Tree
	Hole Depth (Metric)	9.9mm
	Identification Plate Position	none
	Length L2 (Metric)	15.5mm
	Releasable Closure	No
	Tie Closure	plastic pawl
	Width W (Imperial)	0.21"
	Width W (Metric)	5.3mm

157-00017



Product Dimensions	Width W2 (Imperial)	0.3"
	Width W2 (Metric)	7.5mm
	Bundle Diameter Min. (Metric)	1.6mm
	Bundle Diameter Max. (Imperial)	1.2"
	Bundle Diameter Max. (Metric)	30.0mm
	Disc Diameter (Imperial)	0.63"
	Disc Diameter (Metric)	16.0mm
	Panel Thickness Max. (Imperial)	0.18"
	Panel Thickness Max. (Metric)	4.50mm
	Panel Thickness Min. (Metric)	0.6mm
	Mounting Hole Diameter D (Imperial)	0.27 - 0.28"
	Mounting Hole Diameter D (Metric)	6.8 - 7.2 mm
	Thickness T (Imperial)	0.055"
	Thickness T (Metric)	1.4mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987