

157-00402

# HellermannTyton



Article Number: 157-00402

Description: Wide Strap Cable Tie with .25" Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag

Base Data		
	Local Order Number	157-00402
	Type	WSR250
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Mount provides low insertion and high extraction forces which makes for a strong and easy installation.</li> <li>• Clamping rails increase grip on round bundles.</li> <li>• Thinner strap provides increased flexibility for improved ergonomics.</li> <li>• Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.</li> </ul>
	Quantity Per	bag
	Product Description	Wide Strap Heavy Duty Cable Ties features a stud mount for direction application onto a 1/4" threaded stud. The tie is 0.5" wide, and handles bundles from 0.38" - 4.2". The low profile mount design engages a minimum of 4 threads on the stud which makes it easier to apply additional mounts onto one stud.
	Short Description	Wide Strap Cable Tie with .25" Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag
Product Dimensions		
	Minimum Tensile Strength (Imperial)	120.0lbs
	Minimum Tensile Strength (Metric)	534N
	Length L (Imperial)	15.7"
	Length L (Metric)	389.0mm
	Fixation Method	Weld Stud Fixing
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Bundle Diameter Min. (Imperial)	0.38"
	Bundle Diameter Min. (Metric)	9.5mm

157-00402



Product Dimensions	Bundle Diameter Max. (Imperial)	4.1"
	Bundle Diameter Max. (Metric)	104.1mm
	Stud Diameter (Imperial)	0.25"
	Stud Diameter (Metric)	6.35 mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	300
	Package Quantity (Metric)	300Bag
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces