

166-90330

HellermannTyton

Article Number: 166-90330



Description: HelaGuard Non-Metallic IP66 Fitting, Straight, M63" Metric Thread, 2" Dia, PA66, Black, 1/pkg

Base Data		
	Local Order Number	166-90330
	Type	HG200-S-M63
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, M63" Metric Thread, 2" Dia, PA66, Black, 1/pkg
Product Dimensions		
	Length L (Imperial)	2.76"
	Length L (Metric)	70mm
	Outside Diameter D (imperial)	3.54"
	Outside Diameter OD (metric)	90mm
	Nominal Diameter (Imperial)	2-5/8"
	Nominal Diameter (Metric)	67mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2

166-90330



Material and Specifications	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	1Pieces