

166-90513

HellermannTyton



Article Number: 166-90513

Description: Metallic Compression Fitting, 90-Elbow, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg

Base Data		
	Local Order Number	FSU16-M20-C90
	Type	FSU16-M20-C90
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit. • Fitting includes elastomeric sealing washer for IP65 ingress protection. • Suitable for knockouts or Metric threaded entries.
	Quantity Per	pack
	Product Description	Multi-part 90 degree elbow compression fitting with fixed external metric thread pattern suitable for threaded or knockout entries. Constructed with nickel plated brass components that resist corrosion, ensures high mechanical strength and electrical continuity. Fitting comprised of body, nut, grounding ferrule and nylon compression seal. For use with FSU, FPU, and LFHU flexible metal conduits.
	Technical Description	Manufacturer Reference Number: FSU16-M20-C90
	Short Description	Metallic Compression Fitting, 90-Elbow, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.54"
	Length L (Metric)	39.0mm
	Bore Diameter (Imperial)	0.45"
	Bore Diameter (Metric)	11.5mm
	Thread Length (Imperial)	0.51"
	Thread Size (Imperial)	1-1/2 "
	Wrenching Flat Size (Imperial)	1.54"
	Wrenching Flat Size (Metric)	39.0mm
	Height H (Imperial)	1.02"
	Height H (Metric)	26.0mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16.0mm

166-90513

HellermannTyton

Product Dimensions	Thread Length (metric)	13mm
	Thread Size (Metric)	M20
Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	PA6
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces