

170-03157

# HellermannTyton



Article Number: 170-03157

Description: Braided Sleeve, Hook & Loop, Flame Retardant, 2.5" Dia, PET, Black, 100 ft/bulk reel

Base Data		
	Local Order Number	170-03157
	Type	BSHKLPR212B
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Flexible construction that conforms to irregular shapes and contours.</li> <li>• Hook and loop feature wraps over cable bundle allowing future access to cables.</li> <li>• Easy access saves assembly time and allows for easy splicing or insertion of additional wires.</li> </ul>
	Quantity Per	reel
	Product Description	Flame retardant expandable braided sleeving with hook & loop strip for wrapping around cable assemblies. Color matched hook & loop closure provides an easy on and off installation, as well as convenient access for harness break-outs.
	Short Description	Braided Sleeve, Hook & Loop, Flame Retardant, 2.5" Dia, PET, Black, 100 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Bundle Diameter Max. (Imperial)	2.5"
	Bundle Diameter Max. (Metric)	63.5mm
	Nominal Diameter (Imperial)	2-1/2"
	Nominal Diameter (Metric)	63.5mm
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	US MILSPEC	MIL-STD-202
	Flammability	VW-1
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)

170-03157



Material and Specifications	ROHS Compliant	Yes
	Certification/Specification	MIL-STD-202 VW-1
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	1.70kg
	Weight (imperial)	3.75lbs