

170-03211



Article Number: 170-03211

Description: Braided Sleeving, Split Wrap, 3/16" Dia, PET, Black, 1200 ft/bulk reel



Base Data		
	Local Order Number	170-03211
	Type	BSSWV190B
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Center-slit overlapping design allows quick and easy access to the wires and cables for future maintenance or inspection without disassembly.</li> <li>• Flexible material allows it to easily wrap around a variety of component shapes and sizes, making it easier to use than slit-loom tubing or spiral-wrap materials.</li> <li>• A unique weave pattern provides increased coverage and greater resistance to abrasion, dust and debris.</li> <li>• Overlapping design enhances flexibility, allowing it to shift and bend without exposing wire and cables.</li> </ul>
	Quantity Per	box
	Product Description	Split Wrap Woven Sleeving is a self-closing sleeving manufactured from a unique blend of monofilament and multifilament polyester fibers that resemble a tightly woven material. The wrap around design provides increased flexibility, better coverage and greater resistance from abrasion for wires, cables and assemblies. Can also be used to reduce noise in applications that involve movement, while protecting sensitive electronics and communication systems from dust and debris.
	Short Description	Braided Sleeving, Split Wrap, 3/16" Dia, PET, Black, 1200 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	1200.0ft
	Reel Length (imperial)	1200.0ft
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	VW-1
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes

170-03211



Logistic and Packaging		
	Package Quantity (Imperial)	1200ft
	Package Quantity (Metric)	365.76m