



SPECIFICATION SHEET

08-K300PD



KUT-GARD® KNIT KEVLAR® GLOVE WITH PVC DOT GRIP - MEDIUM WEIGHT

- Kut-Gard® 100% Kevlar®, 7 gauge, medium weight
- Dupont Kevlar® brand fiber provides high tensile strength relative to its weight - up to five times stronger than steel
- Kevlar® yarn is designed to be cut resistant
- Kevlar® will not melt, ignite or conduct electricity
- Seamless knit construction protects hands without sacrificing comfort or dexterity
- PVC dots provide enhanced grip and extra cut and abrasion resistance
- Dotted on one side
- Color coded cuffs to easily identify size

APPLICATIONS

- Glass handling
- Canning and bottling
- Sheet metal handling
- Recycling
- Automotive applications

CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spin extract using high speed. Tumble dry on Low to Medium heat setting. Can be Dry-Cleaned. DO NOT BLEACH.

TECHNICAL DATA

MATERIAL	Kevlar®, PVC
COLOR	Shell: ■ Yellow, PVC Dots: ■ Blue
CUFF STYLE	Elastic knit
SIZES	S - XL
PACKAGING	1 pair per bag, 12 pairs per dozen, 12 dozen per case
CASE	20" x 13" x 16" / 50.8cm x 33cm x 40.6cm
CASE WEIGHT (S-XL)	19 lbs / 8.6 kg
COO	USA

PERFORMANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	BAG	DOZEN	CASE
■ 08-K300PD/S	---	01616314003226	02616314003226
■ 08-K300PD/M	---	01616314003233	02616314003233
■ 08-K300PD/L	---	01616314003240	02616314003240
■ 08-K300PD/XL	---	01616314003257	02616314003257



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.0 / 22.9	10.0 / 25.4	10.5 / 26.7	11.0 / 27.9
B	3.6 / 9.1	4.0 / 10.2	4.1 / 10.4	4.3 / 10.9
H	■ White	■ Red	■ Yellow	■ Green

