



# SPECIFICATION SHEET

## 09-K1660



### G-TEK® CRA KNIT KEVLAR® GLOVE WITH NITRILE COATED MICROSURFACE GRIP - MEDIUM WEIGHT

- Seamless knit construction provides comfort without sacrificing dexterity
- Kevlar® fiber shell provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity
- Nitrile "MicroSurface" coated palm and fingertips provide a superior grip in dry, wet and oily conditions by reacting like tiny suction cups that attach themselves firmly to the material being handled
- Knit Wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing

### APPLICATIONS

- Assembly
- Automotive
- Machine operation
- Oily material handling

### CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry cleaned. DO NOT BLEACH.

### TECHNICAL DATA

MATERIAL	Kevlar® / nitrile				
COLOR	Shell: Yellow / Coating: Black				
CUFF STYLE	Elastic knit				
SIZES	S - XXL				
PACKAGING	12 pairs per dozen, 6 dozen per case				
CASE	22.4" x 13.4" x 7.5" / 57cm x 34cm x 19cm				
CASE WEIGHT	S	M	L	XL	XXL
	11.0 lbs 5.0 kg	12.1 lbs 5.5 kg	13.2 lbs 6.0 kg	14.3 lbs 6.5 kg	15.4 lbs 7.0 kg
COO	China				

### PERFORMANCE PROPERTIES

EN388: 4343 ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)  
ASTM F1790-05 ANSI Cut Level 2

ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-


### BARCODES

ITEM	BAG	DOZEN	CASE
09-K1660/S	---	01616314096494	02616314096493
09-K1660/M	---	01616314096500	02616314096509
09-K1660/L	---	01616314096531	02616314096530
09-K1660/XL	---	01616314096517	02616314096516
09-K1660/XXL	---	01616314096524	02616314096523



### DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.3 / 23.5	9.6 / 24.5	10.2 / 26.0	10.4 / 26.5	10.8 / 27.5
B	3.1 / 8.0	3.3 / 8.3	3.6 / 9.2	3.7 / 9.5	4.1 / 10.3
H	Blue	Gold	Purple	Green	Grey



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobal.com](http://www.pipglobal.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.