




SPECIFICATION SHEET

120-4800



MAXIMUM SAFETY® THINSULATE® LINED WINTER GLOVE WITH WATERPROOF BARRIER AND GOATSKIN LEATHER PALM

- Goatskin leather palm is the softest, most abrasion-resistant leather and is highly recommended for applications requiring tactile sensitivity
- 3M™ Thinsulate™ lining provides superior insulation without the bulk of fleece
- PVC diamond grip on fingers and palm for an enhanced grip
- Neoprene pad offers added protection on the knuckles
- Lycra fabric binding for comfort and long lasting wear
- Spandex fabric upper fourchettes between the fingers enhance the natural contour of the glove for a better fit
- Inner knit wrist helps prevent dirt and debris from entering the glove
- Reflective stripes on back for added visibility in low-light

APPLICATIONS

- Petrochemical
- Heavy/Light Construction
- Auto Repair
- Demolition
- Manufacturing
- Mining
- Fabrication
- Landscaping

CARE INSTRUCTIONS

Hand wash only, do not bleach. Hang dry, do not iron.

TECHNICAL DATA

MATERIAL	Goatskin leather, Spandex / Nylon, Polyester
CONSTRUCTION	Back: : Spandex fabric (96% nylon, 4% spandex), + black play boy polyester fabric Palm: 100% goatskin leather with PVC diamond grip patches Fingers: Spandex fabric (96% nylon, 4% spandex) Lining: Complete micro-fleece + Thinsulate C40 gram + Hipora Knuckles: Neoprene 3.0mm Cuff: Black color knit wrist
COLOR	Yellow / Black
CUFF STYLE	Knitwrist
SIZES	S - XXL
PACKAGING	12 pairs per dozen, 6 dozen per case
CASE	22" x 15.7" x 12.6" / 56cm x 40cm x 32cm
CASE WEIGHT	18 lbs / 8.2 g
COO	Pakistan

PERFORMANCE PROPERTIES

EN388: 3121						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-




BARCODES

ITEM	PAIR	DOZEN	CASE
120-4800/S	616314121869	01616314121868	02616314121867
120-4800/M	616314121852	01616314121851	02616314121850
120-4800/L	616314121845	01616314121844	02616314121843
120-4800/XL	616314121876	01616314121875	02616314121874
120-4800/XXL	616314121883	01616314121882	02616314121881

DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.5 / 24.1	9.9 / 25.1	10.3 / 26.1	10.7 / 21.7	11 / 28
B	4.5 / 11.4	4.75 / 12	5 / 12.7	5.25 / 13.3	5.5 / 14

Tolerance (in): +/- 0.125



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.