

190-00149

Article Number: 190-00149

Description: Snapper Hose Clamp, 1.49"–1.59" Bundle Diameter, PA66GF13, Black, 50/pkg



Base Data	Local Order Number	SNP34GHS0K2
	Type	SNP34
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Designed for quick, ratcheted installation and can be released and reused.</li> <li>• Heat stabilized material is suitable for high temperature applications.</li> </ul>
	Quantity Per	bag
	Product Description	<p>Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments.</p> <p>A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends.</p> <p>Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases.</p> <p>The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.</p>
	Short Description	Snapper Hose Clamp, 1.49"–1.59" Bundle Diameter, PA66GF13, Black, 50/pkg
Product Dimensions	Fixation Method	Plug-in mounting
	Variant	Closed
	Width W2 (Imperial)	0.292"
	Width W2 (Metric)	7.42mm
	Bundle Diameter Min. (Imperial)	1.38"
	Bundle Diameter Min. (Metric)	35.0mm
	Bundle Diameter Max. (Imperial)	1.6"
	Bundle Diameter Max. (Metric)	40.5mm
	Diameter Min. (Imperial)	1.365"

190-00149

**HellermannTyton**

Product Dimensions	Diameter Min. (Metric)	34.67mm
	Diameter Max. (Imperial)	1.593"
	Diameter Max. (Metric)	40.46mm
	Wall Thickness WT (Imperial)	.069"
	Wall Thickness WT (Metric)	1.7mm
Material and Specifications		
	Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
	Material Shortcut	PA66GF13
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50
	Customs Number(Schedule B)	3926909987