

309-65223

HellermannTyton

Article Number: 309-65223

Description: Heat Shrink Tubing, 4' Long Stick, 2:1 Shrink Ratio, 3.0", 76.2/38.1 Dia, PO, Blue, 3/pkg



Base Data	
Local Order Number	309-65223
Type	TFN21-ST 76.2/38.1
Color	Blue (BU)
Features and benefits	<ul style="list-style-type: none"> • Thin, 2 to 1 shrink ratio tubing provides insulation and abrasion protection for wires and cables. • Flammability rating of UL224 VW-1 for use in applications requiring the highest degree of flame protection (excludes clear tubing). • Flexible-yet-durable material resists most common oils, chemicals and fluids. • Available in a variety of diameters and colors for identifying and marking wires and cables. • Available in mini reels, bulk reels, and sticks for small to large volume applications.
Quantity Per	pack
Product Description	TFN21 is a highly flexible thin wall heat shrink tubing with a 2 to 1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. Available in mini reels, bulk reels and sticks, for small to large volume applications.
Short Description	Heat Shrink Tubing, 4' Long Stick, 2:1 Shrink Ratio, 3.0", 76.2/38.1 Dia, PO, Blue, 3/pkg
Product Dimensions	
Length L2 (Imperial)	4.0ft
Length L2 (Metric)	1.22m
Printable (Yes/No)	Yes
Shrink Ratio	2:1
Trade Size	3 "
Variant	Thin-Wall
Volume Resistance (Ohm cm)	10 ¹⁴ Ω cm
Nominal Diameter (Imperial)	3"
Nominal Diameter (Metric)	76.2mm
Wall Thickness WT (Imperial)	.047"
Wall Thickness WT (Metric)	1.20mm

309-65223



Product Dimensions	Recovered Diameter d (metric)	38.1mm
	Recovered Diameter d (imperial)	1.5"
	Supplied Diameter D (metric)	76.2mm
	Supplied Diameter D (imperial)	3.0"
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	Dielectric Strength (Metric)	20 kV/mm
	Elongation at break	600%
	Flammability	UL 224 VW-1
	Halogenfree	No
	Shrink Temperature	+158 °F (+70 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 224
UL Recognized (US)	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	3
	Package Quantity (Metric)	3