



SPECIFICATION SHEET

120-5300



MAXIMUM SAFETY® ROUSTABOUT II

- Synthetic leather palm with silicone grip enhances grip in wet and dry applications while providing dexterity
- Thermo Plastic Rubber (TPR) molded fingers, thumb and back of the hand guards for maximum protection
- Kevlar® Stitched palm for added durability and gel padding for comfort
- Synthetic Leather forchettes enhance the natural contour of the glove for a better fit
- Kevlar® Fabric reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in high-wear areas
- Hi-Vis Spandex fabric back
- Glove pull with ID badge on wrist for ease of donning
- Launderable for extended life and to reduce replacement costs

APPLICATIONS

- Petrochem
- Construction
- Demolition
- Mining
- Fabrication

CARE INSTRUCTIONS

Machine wash in cold water, do not bleach, hang dry, do not iron.

TECHNICAL DATA

MATERIAL	Synthetic leather / Spandex			
COLOR	Orange / Black			
CUFF STYLE	Slip on			
SIZES	M - XXL			
PACKAGING	1 pair per bag, 72 pair per case			
CASE	24.5" x 15.5" x 13.5" / 62.2cm x 39.4cm x 34.3cm			
CASE WEIGHT	M	L	XL	XXL
	46.3 lbs 21 kg	47.4 lbs 21.5 kg	48.5 lbs 22 kg	47.6 lbs 22.5 kg
COO	Pakistan			

PERFORMANCE PROPERTIES

EN388: 3132						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	PAIR	DOZEN	CASE
120-5300/M	616314160103	01616314160102	02616314160101
120-5300/L	616314160110	01616314160119	02616314160118
120-5300/XL	616314160134	01616314160133	02616314160132
120-5300/XXL	616314160141	01616314160140	02616314160149



DIMENSIONS (in/cm)

	M	L	XL	XXL
A	10.1 / 25.7	10.5 / 26.7	10.9 / 27.7	11.1 / 28.2
B	4.3 / 10.8	4.5 / 11.4	4.8 / 12.1	5.0 / 12.7
C	2.75 / 7.0	2.75 / 7.0	2.75 / 7.0	2.75 / 7.0

