

553-50176



Article Number: 553-50176

Description: Heat Shrink Labels, .187" (4.74mm) 1-Slit Single Sided, PO-X, White, 10,000/box



Base Data		
	Local Order Number	553-50176
	Type	HST4.8-1.6WH-S
	Color	White (WH)
	Features and benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
	Quantity Per	box
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Short Description	Heat Shrink Labels, .187" (4.74mm) 1-Slit Single Sided, PO-X, White, 10,000/box
Product Dimensions		
	Length L (Imperial)	0.95"
	Length L (Metric)	24.0mm
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Width W (Imperial)	1.9"
	Width W (Metric)	48.0mm
	Height H (Imperial)	0.31"
	Height H (Metric)	7.9mm
	Diameter Max. (Imperial)	0.187"
	Outside Diameter Max. (Imperial)	0.187"
	Outside Diameter Max. (Metric)	4.74mm
	Wall Thickness WT (Imperial)	0.026"
	Wall Thickness WT (Metric)	0.66mm

553-50176



Product Dimensions	Flexibility	Flexible
	Print Method	Thermal transfer
	Recovered Diameter d (metric)	1.6mm
	Recovered Diameter d (imperial)	0.063"
	Supplied Diameter D (imperial)	0.177"
	Supplied Diameter D (metric)	4.5mm
	Thickness T (Metric)	3.0µm
	Width of Liner WL (imperial)	3.0"
	Width of Liner WL (metric)	76.2mm
	Width of printable area (metric)	16.08mm
	Width of Printable Area (imperial)	0.63"
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	MIL-STD-202G Method 215K
	Dielectric Strength (Metric)	19.7 kV min.
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging	Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3
	Package Quantity (Imperial)	10000
	Package Quantity (Metric)	10000
	Customs Number(Schedule B)	3926909987
	Markers per row	2
	Content Unit (BMEcat)	pack
	Weight (Metric)	0.1kg