



SPECIFICATION SHEET

15-210



4544

G-TEK® SUPRENE™ BLENDED GLOVE WITH NITRILE COATED MICROSURFACE GRIP

- Suprene™ fiber shell is 100 times stronger than steel and is amongst the highest performing fibers in cut and tear resistance
- Seamless knit construction provides comfort without sacrificing dexterity
- Nitrile MicroSurface coated palm and fingertips provide a superior grip in dry, wet and oily conditions by reacting like tiny suction cups that attach themselves firmly to the material being handled
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Launderable for extended life and to reduce replacement costs

APPLICATIONS

- Electronics
- General duty
- Parts assembly
- Construction

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	Suprene™ Engineered Yarn / Nitrile MicroSurface Coating					
CONSTRUCTION	Seamless Knit					
COLOR	Shell: ■ Tan / Coating: ■ Black					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case					
CASE DIMENSIONS	15" x 11.8" x 10.6" / 38cm x 30cm x 27cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	7.5 lbs	8 lbs	8.8 lbs	10.4 lbs	11 lbs	11.3 lbs
	3.4 kgs	3.7 kgs	4 kgs	4.7 kgs	4.9 kgs	5.2 kgs
COO	China					

PERFORMANCE PROPERTIES

EN388: 4544	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-


BARCODES

ITEM	BAG	DOZEN	CASE
15-210/XS	616314219177	01616314219176	02616314219175
15-210/S	616314219153	01616314219152	02616314219151
15-210/M	616314219146	01616314219145	02616314219144
15-210/L	616314219139	01616314219138	02616314219137
15-210/XL	616314219160	01616314219169	02616314219168
15-210/XXL	616314219184	01616314219183	02616314219182



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.6 / 22	9 / 23	9.4 / 24	9.8 / 25	10.2 / 26	10.6 / 27
B	3.4 / 8.8	3.5 / 9	3.7 / 9.5	4 / 10.3	4.1 / 10.6	4.3 / 10.8
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Sky Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.