



SPECIFICATION SHEET

15-215



G-TEK® SUPRENE™ BLENDED GLOVE WITH NITRILE COATED MICROSURFACE GRIP

- Suprene™ fiber shell is 100 times stronger than steel and is amongst the highest performing fibers in cut and tear resistance
- Seamless knit construction provides comfort without sacrificing dexterity
- Nitrile MicroSurface coated palm, fingertips and knuckles provide a superior grip in dry, wet and oily conditions by reacting like tiny suction cups that attach themselves firmly to the material being handled
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Launderable for extended life and to reduce replacement costs

APPLICATIONS

- Electronics
- General duty
- Parts assembly
- Construction

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	Suprene™ Engineered Yarn / Nitrile MicroSurface Coating					
CONSTRUCTION	Seamless Knit					
COLOR	Shell: ■ Tan / Coating: ■ Black					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case					
CASE DIMENSIONS	15" x 11.8" x 10.6" / 38cm x 30cm x 27cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	7.5 lbs 3.4 kgs	8 lbs 3.7 kgs	8.8 lbs 4 kgs	10.4 lbs 4.7 kgs	11 lbs 4.9 kgs	11.3 lbs 5.2 kgs
COO	China					

PERFORMANCE PROPERTIES

EN388: 4544	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
15-215/XS	616314219238	01616314219237	02616314219236
15-215/S	616314219214	01616314219213	02616314219212
15-215/M	616314219207	01616314219206	02616314219205
15-215/L	616314219191	01616314219190	02616314219189
15-215/XL	616314219221	01616314219220	02616314219219
15-215/XXL	616314219245	01616314219244	02616314219243



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.6 / 22	9 / 23	9.4 / 24	9.8 / 25	10.2 / 26	10.6 / 27
B	3.4 / 8.8	3.5 / 9	3.7 / 9.5	4 / 10.3	4.1 / 10.6	4.3 / 10.8
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Sky Blue

