



SPECIFICATION SHEET

19-D650



4342

G-TEK® POLYKOR® SEAMLESS KNIT POLYKOR® BLENDED GLOVE WITH POLYURETHANE COATED SMOOTH GRIP ON PALM & FINGERTIPS

- Seamless construction offers increased comfort and breathability
- PolyKor® shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Polyurethane coated palm and fingertips for great abrasion resistance, excellent puncture resistance and outstanding wet/dry grip
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Washable, resistant to chemicals, water, and ultraviolet light

APPLICATIONS

- Electronics
- Glass cutting
- Metal handling
- Food & meat processing

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 104°F (40°C). A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low, maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Shell: PolyKor® Blend Coating: Polyurethane				
COLOR	Gray				
CUFF STYLE	Continuous Knit				
SIZES	S - XXL				
PACKAGING	1 pair per bag, 12 pairs per dozen, 12 dozen per case				
CASE DIMENSIONS	22" x 12.6" x 14.2" / 56cm x 32cm x 36cm				
CASE WEIGHT	S	M	L	XL	XXL
	16.8 lbs 7.6 kg	18 lbs 8.2 kg	18.7 lbs 8.5 kg	21 lbs 9.5 kg	21.6 lbs 9.8 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 4342 ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
ASTM F1790-05 ANSI Cut Level 2

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5


BARCODES

ITEM	BAG	DOZEN	CASE
19-D650/S	---	01616314046369	02616314046368
19-D650/M	---	01616314046352	02616314046351
19-D650/L	---	01616314046345	02616314046344
19-D650/XL	---	01616314046376	02616314046375
19-D650/XXL	---	01616314048936	02616314048935



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.1 / 23	9.4 / 24	9.8 / 25	10.2 / 26	10.6 / 27
B	3.5 / 9	3.7 / 9.5	3.9 / 10	4.1 / 10.5	4.1 / 10.5
H	Red	Yellow	Brown	Black	Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.