

553-50189



Article Number: 553-50189

Description: Heat Shrink Labels, .38" (9.52mm), Single Sided, 3-Slit, PO-X, Black, 1000/box



Base Data		
	Local Order Number	553-50189
	Type	HST9-3BK-3S
	Color	Black (BK)
	Features and benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
	Quantity Per	reel
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Short Description	Heat Shrink Labels, .38" (9.52mm), Single Sided, 3-Slit, PO-X, Black, 1000/box
Product Dimensions		
	Length L (Imperial)	0.475"
	Length L (Metric)	12.07mm
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Height H (Imperial)	.24"
	Height H (Metric)	5.97mm
	Diameter Max. (Imperial)	0.125"
	Diameter Max. (Metric)	3.18mm
	Outside Diameter Max. (Imperial)	0.375"
	Outside Diameter Max. (Metric)	9.52mm
	Wall Thickness WT (Imperial)	0.031"
	Wall Thickness WT (Metric)	0.79mm
	Flexibility	Flexible

553-50189



Product Dimensions	Print Method	Thermal transfer
	Recovered Diameter d (metric)	3.1mm
	Recovered Diameter d (imperial)	0.122"
	Supplied Diameter D (imperial)	0.354"
	Supplied Diameter D (metric)	9.0mm
	Thickness T (Metric)	3.0µm
	Width of Liner WL (metric)	76.2mm
	Width of Liner WL (imperial)	3.0"
	Width of Printable Area (imperial)	0.474"
	Width of printable area (metric)	12.07mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	SAE-AS81531
	Dielectric Strength (Metric)	19.7 kV min.
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Markers per row	4
	Content Unit (BMEcat)	pack
	Weight (imperial)	0.93lbs
	Weight (Metric)	0.43kg