

553-50239



Article Number: 553-50239

Description: Heat Shrink Labels, .187" (4.74mm), Single Sided, 3-Slit, PO-X, Yellow, 1000/box



Base Data		
	Local Order Number	553-50239
	Type	HST4.8-1YE-3S
	Color	Yellow (YE)
	Features and benefits	<ul style="list-style-type: none"> <li>• Slide Slit and optional center slits for easy wire insertion.</li> <li>• Smooth surface for clean and legible printing.</li> <li>• Supplied on a ladder style carrier so that markers can be kitted after printing.</li> <li>• A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.</li> </ul>
	Quantity Per	pack
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Short Description	Heat Shrink Labels, .187" (4.74mm), Single Sided, 3-Slit, PO-X, Yellow, 1000/box
Product Dimensions		
	Length L (Imperial)	0.312"
	Length L (Metric)	7.92mm
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Height H (Imperial)	.31"
	Height H (Metric)	7.90mm
	Diameter Max. (Imperial)	0.187"
	Outside Diameter Max. (Imperial)	0.187"
	Outside Diameter Max. (Metric)	4.74mm
	Wall Thickness WT (Imperial)	0.026"
	Wall Thickness WT (Metric)	0.66mm
	Flexibility	Flexible
	Print Method	Thermal transfer

553-50239



Product Dimensions	Recovered Diameter d (metric)	1.6mm
	Recovered Diameter d (imperial)	0.063"
	Supplied Diameter D (metric)	4.5mm
	Supplied Diameter D (imperial)	0.177"
	Thickness T (Metric)	3.0µm
	Width of Liner WL (imperial)	3.0"
	Width of Liner WL (metric)	76.2mm
	Width of printable area (metric)	12.07mm
	Width of Printable Area (imperial)	0.475"
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	SAE-AS81531
	Dielectric Strength (Metric)	19.7 kV min.
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging	Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Markers per row	4
	Weight (imperial)	1.36lbs
	Weight (Metric)	0.635kg