



SPECIFICATION SHEET

19-D655



G-TEK® POLYKOR® SEAMLESS KNIT POLYKOR® BLENDED GLOVE WITH POLYURETHANE COATED SMOOTH GRIP ON PALM & FINGERS & KNUCKLES

- Seamless construction offers increased comfort and breathability
- PolyKor™ shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Polyurethane coated palm and knuckles for great abrasion resistance, excellent puncture resistance and outstanding wet/dry grip
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Washable, resistant to chemicals, water, and ultraviolet light

APPLICATIONS

- Electronics
- Glass cutting
- Metal handling
- Food and meat processing

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 104°F (40°C). A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low, maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Shell: PolyKor® Blend Coating: Polyurethane			
COLOR	■ Black & Gray / ■ Black			
CUFF STYLE	Continuous Knit			
SIZES	S - XL			
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case			
CASE DIMENSIONS	22" x 12.6" x 14.2" / 56cm x 32cm x 36cm			
CASE WEIGHT	S	M	L	XL
	19.8 lbs 9 kg	20.4 lbs 9.3 kg	22.2 lbs 10.1 kg	24 lbs 10.9 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 4341	ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16) ASTM F1790-05 ANSI Cut Level 2					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 19-D655/S	---	01616314046451	02616314046450
■ 19-D655/M	---	01616314046437	02616314046436
■ 19-D655/L	---	01616314046444	02616314046443
■ 19-D655/XL	---	01616314046468	02616314046467



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.1 / 23	9.4 / 24	9.8 / 25	10.2 / 26
B	3.7 / 9.5	3.7 / 9.5	3.9 / 10	4.1 / 10.5
H	Red	Yellow	Brown	Black

