

596-00648

# HellermannTyton

Article Number: 596-00648



Description: Pre-Printed Header Label, DANGER, 3.0" x 2.0", UV, PET, Red, 250/roll

Base Data		
	Local Order Number	596-00648
	Type	3X2DANGERUV
	Color	Red (RD)
	Features and benefits	<ul style="list-style-type: none"> <li>• Made with UV stable inks and materials for durability and weather resistance.</li> <li>• Supplied with an aggressive adhesive to ensure long life.</li> <li>• Meets NEC &amp; IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.</li> <li>• Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.</li> </ul>
	Quantity Per	reel
	Product Description	HellermannTyton Pre-Printed Vinyl Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
	Technical Description	Pre-Printed Header Label, DANGER, 3" X 2", UV, Red
	Short Description	Pre-Printed Header Label, DANGER, 3.0" x 2.0", UV, PET, Red, 250/roll
Product Dimensions		
	Length L (Imperial)	2.0"
	Length L (Metric)	50.8mm
	Width W (Imperial)	3.0"
	Width W (Metric)	76.2mm
	Height H (Imperial)	2.0"
	Height H (Metric)	50.80mm
	Horizontal Repeat HR (metric)	76.2mm
	Horizontal Repeat HR (imperial)	3.0"
	Width of Liner WL (metric)	81.28mm
	Width of Liner WL (imperial)	3.2"

596-00648



Material and Specifications		
	Material	Type 840/926, Polyester (PET), white (WH) UV stable w/ clear Polyester laminate
	Material Shortcut	840/926
	Halogenfree	Yes
	Operating Temperature	-40°F to +302°F (-40°C to +150°C)
	ROHS Compliant	Yes
	Certification/Specification	ANSI Standard Z535.4
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	250
	Package Quantity (Metric)	250
	Customs Number(Schedule B)	3919102055
	Labels per Column	1
	Labels per Row	1
	Weight (imperial)	3.2oz