


596-00920

HellermannTyton

Article Number: 596-00920



Description: Metal Solar Placard, 2017 Code, WARNING ELECTRICAL...DC VOLTAGE, 3.75" x 2.5", AL,Orange/Silver,5/pkg

Base Data		
	Local Order Number	596-00920
	Type	WESHLBLDC17M5
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> • Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure. • Aggressive adhesive ensures strong bond, even on powder coated surfaces. • Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability. • Optional Paint Shields provide additional protection for pre-printed and variable data placards.
	Quantity Per	pack
	Product Description	Metal Solar Placards offer maximum durability for labeling photovoltaic equipment and components. A special printing process fuses UV stable inks to the placards for long-lasting results, tested to last up to 25 years—even in direct sunlight. Metal Solar Placards are designed to meet or exceed National Electrical Code (NEC) and the requirements of local Authorities Having Jurisdiction (AHJs), that may prefer a placard-style marking over thermal transfer printed labels.
	Technical Description	3.75" X 2.5" Black text on an Orange/Silver Aluminum background that reads as: "WARNING ELECTRICAL SHOCK HAZARD. TERMINALS ON BOTH LINE AND LOAD SIDE MAY BE ENERGIZED IN THE OPEN POSITION. DC VOLTAGE IS ALWAYS PRESENT WHEN SOLAR MODULES ARE EXPOSED TO SUNLIGHT" - 5 per pack
	Short Description	Metal Solar Placard, 2017 Code, WARNING ELECTRICAL...DC VOLTAGE, 3.75" x 2.5", AL,Orange/Silver,5/pkg
Product Dimensions		
	Length L (Imperial)	2.5"
	Length L (Metric)	63.5mm
	Width W (Imperial)	3.75"
	Width W (Metric)	95.25mm
	Height H (Imperial)	2.50"
	Height H (Metric)	63.50mm

596-00920



Material and Specifications		
	Material	Anodized Aluminum (AA)
	Material Shortcut	AA
	Adhesive	Ultra High Bond Permanent Acrylic Adhesive
	Halogenfree	Yes
	Operating Temperature	-40°F to +203°F (-40°C to +95°C)
	ROHS Compliant	Yes
	Certification/Specification	NEC2017
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5
	Customs Number(Schedule B)	3919102055