



SPECIFICATION SHEET

280-ML5151

COMFORT PLUS™ 5151 CAP STYLE HARD HAT

- High-density polyethylene (HDPE) shell dissipates impact energy
- Shock-absorbing 6-point suspension with adjustable 1" wide polyester textile straps
- Pivoting wheel ratchet adjustment easily fits over the nape of the neck for a secure fit
- Brushed nylon backed foam sweatband
- Universal slots to accept various accessories
- Packed ready-to-wear with no assembly required
- Meets ANSI/ISEA Z89.1-2014, Type I, Class G requirements

APPLICATIONS

Protection from falling debris, low hanging objects, and electrical hazards

CARE INSTRUCTIONS

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

TECHNICAL DATA

MATERIAL	Shell: HDPE; Webbing: LDPE Strap; Harness: LDPE Harness Clips, Polyester Crown Straps Comes with Brushed Nylon Backed Foam Sweatband		
COLOR	<input type="checkbox"/> White (10) <input type="checkbox"/> Yellow (20) <input type="checkbox"/> Green (30) <input type="checkbox"/> Pink (39)	<input type="checkbox"/> Blue (50) <input type="checkbox"/> Red (60) <input type="checkbox"/> Orange (80)	
SIZES	Adjustable		
HAT SIZE	6 1/2" - 7 1/2"		
WEIGHT	14.1oz / 400 grams		
PACKAGING	1 per polybag; 35 per case		
CASE	30" x 23" x 17" / 76cm x 58cm x 43cm		
CASE WEIGHT	36 lbs / 16.3 kg		
COO	UAE		

BARCODES

ITEM	EACH	CASE
<input type="checkbox"/> 280-ML5151-10	5038428119856	5038428811088
<input type="checkbox"/> 280-ML5151-20	5038428119863	5038428811095
<input type="checkbox"/> 280-ML5151-30	5038428119870	5038428811125
<input type="checkbox"/> 280-ML5151-39	5038428143639	5038428812344
<input type="checkbox"/> 280-ML5151-50	5038428119887	5038428811101
<input type="checkbox"/> 280-ML5151-60	5038428119894	5038428811118
<input type="checkbox"/> 280-ML5151-80	5038428119900	5038428811132



DIMENSIONS (in/cm)

	OSFA			
A	11.25 / 28.6			
B	5.5 / 14			

