



SPECIFICATION SHEET

302-USV5



ANSI TYPE R CLASS 2 TWO-TONE PREMIUM EXPANDABLE MESH VEST

- Breathable polyester mesh
- 2" two-tone reflective tape
- Zipper closure
- Adjustable sides for a comfortable fit
- 1 internal chest pocket
- 2 internal lower pockets
- Available in hi-vis lime yellow or hi-vis orange

APPLICATIONS

- Roadway construction workers
- Survey crews
- Utility workers
- Railway and metro workers
- Emergency response personnel

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 30 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120g/m ² 100% polyester 5*1 mesh fabric; #5 resin zipper
COLOR	■ Hi-Vis Lime Yellow or ■ Hi-Vis Orange
SIZES	One Size (Adjustable)
PACKAGING	1/Polybag, 50/Case
CASE	20.5" x 11" x 18.1" / 52cm x 28cm x 46cm
CASE WEIGHT	26.5 lbs / 12 kg
COO	China

BARCODES

ITEM	BAG	DOZEN	CASE
■ 302-USV5-LY	01616314077042	---	02616314077041
■ 302-USV5-OR	01616314074003	---	02616314074002



DIMENSIONS (in/cm)

	OSFM					
A	49.6 / 126					
B	24.8 / 63					

