

Article Number: 859-30035

Description: RNG Series Modular Panel with Rack-Snaps, 2U, Black,

1/ctn



Base Data		
	Local Order Number	RNGPP2URS
	Туре	RNA6UXX-PA2URS-XX.XX
	Color	Black (BK)
	Features and benefits	 1U High Density RNG Series modular panel accepts 4 high density cassettes and provides copper and fiber solutions in the same footprint. 2U RNG Series modular panel accepts 8 RNG Series cassettes and provides copper and fiber solutions in the same footprint. Designed for a quick-and-easy insertion. Rack-Snaps make panel mounting simple.
	Product Description	RapidNet is HellermannTyton's patented pre-terminated "connect and go" system which offers a high performance in copper and fiber solutions for data centers and storage area network applications. These pre-terminated solutions do not require on-site termination or certification testing which dramatically reduces installation time up to 85%.
	Technical Description	RNG Series Modular Panel with Rack-Snaps, 2U, Black
	Short Description	RNG Series Modular Panel with Rack-Snaps, 2U, Black, 1/ctn
Product Dimensions		
	Width W (Imperial)	19.0"
	Width W (Metric)	483.0mm
	Height H (Imperial)	3.6"
	Height H (Metric)	88.0mm
	Depth D (metric)	56.0mm
	Depth D (imperial)	2.2"
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8544493080

generated on: 7/2/2017



generated on: 7/2/2017