



SPECIFICATION SHEET

44-3745



4542

MAXICUT® ULTRA™ BY ATG®, PREMIUM BLUE ENGINEERED YARN SHELL, BLACK MICRO-FOAM NITRILE COATING

- Micro-Foam nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Unique high performance yarns and fibers that offer cut protection while maintaining high levels of comfort
- Reinforcement between the thumb and forefinger
- Patented micro-foam nitrile coating offers 360° breathability making it the most breathable cut resistant glove on the market
- Optimized grip delivered through our micro-cup finish
- Minimal penetration (strike through) leaving only the soft liner resting against the skin
- The Skin Health Alliance has awarded professional dermatological accreditation following review of the scientific dossier behind this product
- Silicone free
- Made from component materials which comply with Federal regulations for food contact 21 CFR 170-199
- This style is also available tri-folded and shrink-wrapped for carefree dispensing through vending machines (44-3745V)

APPLICATIONS

- DIY and Gardening
- Finishing and inspection
- Handling of small components
- Primary, secondary and final assembly
- Maintenance
- Logistics and warehousing
- Using tools and instruments

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Seamless knit engineered yarn, micro-foam nitrile coating						
COLOR	Blue/Black						
CUFF STYLE	Continuous Knit						
SIZES	XS - XXXL						
PACKAGING	12 per dozen, 6 dozen per case						
CASE	19.7" x 11.6" x 7.9" / 50cm x 29.5cm x 20cm						
CASE WEIGHT	XS	S	M	L	XL	XXL	XXXL
	8.8 lbs 4 kg	9.9 lbs 4.5 kg	10.5 lbs 4.75 kg	11 lbs 5 kg	11.9 lbs 5.4 kg	12.5 lbs 5.65 kg	12.8 lbs 5.8 kg
COO	Sri Lanka						

PERFORMANCE PROPERTIES

EN388: 4542	ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)					
	ASTM F1790-05 ANSI Cut Level 3					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5




BARCODES

ITEM	PAIR	DOZEN	CASE
44-3745/XS	616314178528	01616314178527	02616314178526
44-3745/S	616314178504	01616314178503	02616314178502
44-3745/M	616314178498	01616314178497	02616314178496
44-3745/L	616314178481	01616314178480	02616314178489
44-3745/XL	616314178511	01616314178510	02616314178519
44-3745/XXL	616314178535	01616314178534	02616314178533
44-3745/XXXL	616314178542	01616314178541	02616314178540

DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL	XXXL
A	7.87 / 20	8.27 / 21	8.66 / 22	9.6 / 23	9.45 / 24	9.65 / 24.5	9.65 / 24.5
B	3.2 / 8.2	3.4 / 8.6	3.8 / 9.6	3.9 / 9.8	3.9 / 10	4.0 / 10.2	4.1 / 10.4
H	Blue	White	Green	Brown	Yellow	Gray	Purple



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.