



# SPECIFICATION SHEET

## 44-3755



### MAXICUT® ULTRA™ BY ATG®, PREMIUM BLUE ENGINEERED YARN SHELL, BLACK MICRO-FOAM 3/4 DIP NITRILE COATING

- Micro-Foam nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Unique high performance yarns and fibers that offer cut protection while maintaining high levels of comfort
- Reinforcement between the thumb and forefinger
- Patented micro-foam nitrile coating offers 360° breathability making it the most breathable cut resistant glove on the market
- Optimized grip delivered through our micro-cup finish
- Minimal penetration (strike through) leaving only the soft liner resting against the skin
- The Skin Health Alliance has awarded professional dermatological accreditation following review of the scientific dossier behind this product
- Silicone free

### APPLICATIONS

- DIY
- Finishing and inspection
- Gardening
- Handling of small components
- Primary, secondary and final assembly
- Maintenance
- Logistics and warehousing
- Using tools and instruments

### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

### TECHNICAL DATA

MATERIAL	Seamless knit engineered yarn, micro-foam nitrile coating					
COLOR	Blue/Black					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	12 per dozen, 6 dozen per case					
CASE	19.7" x 11.6" x 7.9" / 50cm x 29.5cm x 20cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	9.9 lbs 4.5 kg	10.6 lbs 4.8 kg	11.5 lbs 5.2 kg	12.5 lbs 5.65 kg	13.2 lbs 6 kg	14 lbs 6.35 kg
COO	Sri Lanka					

### PERFORMANCE PROPERTIES

EN388: 4542		ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)				
		ASTM F1790-05 ANSI Cut Level 3				
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5




### BARCODES

ITEM	PAIR	DOZEN	CASE
44-3755/XS	616314178597	01616314178596	02616314178595
44-3755/S	616314178573	01616314178572	02616314178571
44-3755/M	616314178566	01616314178565	02616314178564
44-3755/L	616314178559	01616314178558	02616314178557
44-3755/XL	616314178580	01616314178589	02616314178588
44-3755/XXL	616314178603	01616314178602	02616314178601

### DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.07 / 20.5	8.46 / 21.5	8.86 / 22.5	9.25 / 23.5	9.65 / 24.5	9.84 / 25
B	3.5 / 9	3.6 / 9.2	3.9 / 9.8	4.0 / 10.2	4.2 / 10.7	4.3 / 11
H	Blue	White	Green	Brown	Yellow	Gray



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobal.com](http://www.pipglobal.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.