






PROFILE VIEW REF
SHOWING CLEARANCES
FOR WASHER & SOCKET

VIEW B




TABLE OF PART NUMBERS

PART NUMBER	PART REV	HOLE DIA	BOLT SIZE
HDM320B	B	.327[8,31]	5/16" & 8MM
HDM400B	B	.405[10,29]	3/8" & 10MM
HDM500B	B	.510[12,95]	1/2" & 12MM

FEATURES:

- RUGGED HEAVY DUTY DESIGN & MATERIAL
- 250 lb ASSEMBLY STRENGTH PERPENDICULAR TO BOLT AXIS
- METAL BUSHING WITH STANDS 114 lb-ft (155 N-m) OF TORQUE APPLIED TO FASTENER
- FASTEN MOUNT WITH STUD, BOLT, SCREW, RIVET, SPIKE, ETC...
- CLEARANCE FOR WASHER & SOCKET DURING ASSEMBLY - SEE VIEW B
- ACCEPTS MOST STANDARD CABLE TIES UP TO 1/2" WIDE
- MOUNTS ARE DESIGNED TO BE VERTICALLY STACKED ON A SINGLE FASTENER TO ALLOW DUAL BUNDLING - SEE VIEW C
- ALSO CHAINING OF MULTIPLE BUNDLES ON A SINGLE MOUNT IS AVAILABLE IF T250 WITH BUCKLE/MOUNT FEATURE IS USED
- MOUNTING HOLE DIAMETERS ARE AVAILABLE FROM 5/16" TO 1/2" - SEE TABLE

INVENTORS

HellermannTyton®

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state
G GEIGER	1/5/01	JACKSON, WI

REVISION

level	04
by	GGG
date	1/6/09
ECN #	011204
part level	TABLE

DIMENSIONS

TOLERANCES	.XXXX= ±0.005 / [1,27]
	.XXX= ±0.010 / [2,5]
	.XX= ±0.02 / [5]
	.X= ±0.1 / [6,4]
	∠= ±0.5
unless otherwise specified	
units	inches/mm

PART

number	see table	phase	PRODUCTION
name	HIGH-TORQUE HEAVY-DUTY CABLE TIE MOUNT INSERT-MOLDED WITH METAL BUSHING		
material	NYLON 6/6 HHSUV BLACK		

DRAWING

FORMAT AH version J	CAD	PRO-E	scale 1/1
computer file number	previous number		
drawn G GEIGER	checked K CHRISTIAN	approved	
date 1/5/01	checked 1/6/09	approved	
type CUSTOMER	sheet 1 of 1		
number	MT1022306CST		