



# SPECIFICATION SHEET

## 50-N2250G



### ASSURANCE® UNSUPPORTED NITRILE, FLOCK LINED WITH RAISED DIAMOND GRIP - 22 MIL

- Provides superior resistance to physical hazards such as cut, puncture, snag and abrasion and many chemical hazards including solvents and oil based chemicals
- Straight cuff adds additional length to protect the forearm from liquid run-off
- Unlined to reduce potential of product contamination
- Raised Diamond pattern for an enhanced grip
- Chlorinated to harden and cleanse the surface of the glove
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199

### APPLICATIONS

- Chemical processing
- Oil refining and petrochemicals
- Aerospace and automotive degreasing
- Automotive assembly and painting
- Machining operations
- Metal fabrication
- Graphic arts and printing cleanup
- Furniture manufacturing
- Electronics

### TECHNICAL DATA


MATERIAL	Nitrile			
COLOR	Green			
CUFF STYLE	Straight Cuff			
SIZES	M - XXL			
PACKAGING	12 pairs per dozen, 1 dozen per case			
CASE	17.7" x 10.8" x 11.8" / 45cm x 27.5cm x 30cm			
CASE WEIGHT	M	L	XL	XXL
	4.2 lbs	4.4 lbs	4.9 lbs	5.1 lbs
	1.9 kg	2.0 kg	2.2 kg	2.3 kg
COO	Sri Lanka			

### PERFORMANCE PROPERTIES

EN388: 4102						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

### BARCODES

ITEM	BAG	DOZEN	CASE
50-N2250G/XXL	---	01616314035548	02616314035548
50-N2250G/XL	---	01616314035531	02616314035531
50-N2250G/L	---	01616314035517	02616314035517
50-N2250G/M	---	01616314035524	02616314035524



### DIMENSIONS (in/cm)

	M	L	XL	XXL
A	15 / 38.1	15 / 38.1	15 / 38.1	15 / 38.1
B	4.3 / 11	4.8 / 12.2	5.25 / 13.4	5.45 / 13.9
Thickness: 0.55 mm				

